

ABSPRO BDATM

PP Depth Pleated Filters for the Pharmaceuticals / Absolute Ratings



INDUSTRIES & APPLICATIONS



Food & Beverage: Bottle water, Beers, Wines, Syrups, Soft drinks



Pharmaceuticals:

Membrane pre-filtration



Electronics: Process chemicals, Plating solutions, Wash solutions



Cosmetics: Process water, Alcohol, Creams, Oils



Water treatment: Process water clarification, Membrane pre-filtration

ABSPRO BDA™ are absolute rated polypropylene pleated filters designed for a wide range of both pre-filtration and final filtration with a reliable performance in food, beverage, cosmetic, bio and pharmaceutical applications.

ABSPRO BDA™ are multi-layered polypropylene pleated filters made with very thin fibers. These filters are the ideal choice for high viscosity and high contamination applications by extending the life of the membrane filters and hence reducing filtration costs.

FEATURES & BENEFITS

- Very thin fiber melt-blown media of the filter meet a broad range of performance requirements
- Multi-layered filter media construction with graded density provides consistent and reliable filtration performance
- All polypropylene construction provides excellent chemical compatibility and very low level of extractables
- Available in a wide range of end styles and micron ratings
- All materials of construction are FDA listed and conform to the relevant requirements of 21 CFR 177 and USP <88> Class VI-121°C, plastics

TECHNICAL DATA

Nominal Dimensions

Cartridge 68Ø

· Length: 250, 500, 750, 1000 mm · Inner Diameter: 30 mm

· Outer Diameter : 68mm

CAPI

· Length: 143, 216 mm

· Outer Diameter: 71 mm / 73 mm

CAP II

· Length: 203, 212 mm · Outer Diameter: 97 mm



Shoulder to Shoulder Lenath :

10 inch : 243 mm 20 inch : 490 mm 30 inch : 737 mm 40 inch : 984 mm

Outer Diameter: 68 mm

Capsule series CAP I and CAP II





* For details, see the Appendix II - Capsule Filter Types

Materials of Construction

Filtration Media
Support Media
Inner Core
Outer Cage
End Caps
Shell
Polypropylene
Polypropylene
Polypropylene
Polypropylene

· O-rings / Gaskets Silicone, EPDM, Viton, TEV

56

Max. Operating Temperature

· Cartridge: 80°C (176°F) · Capsules: 60°C (140°F)

Max. Operating Forward Differential Pressure

4 bard (58.0 psid) at 20 °C 3 bard (43.5 psid) at 40 °C 2 bard (29.0 psid) at 60 °C

1 bard (14.5 psid) at 80 °C

Recommended Change Out Differential Pressure

2 bard (29.0 psid)

Micron Ratings

0.6, 1, 2, 3, 5, 10, 20, 30 µm

99.98% (β-Ratio 5000) in accordance with modified ASTM F-795-88

(Single pass, constant flow of 10LPM/10" cartridge, ISO standard dust A3 in water)

Filtration Area

· Cartridge 68Ø : 0.3 m² / 10 inch

· CAP I: 0.06 m² / unit · CAP II: 0.15 m² / unit

Food Contact Compliance

All materials of construction are FDA listed and conform to the relevant requirements of 21 CFR 177

Biological Safety

All materials of construction are conform to the relevant requirements of USP <88> Class VI-121°C, plastics


Particle Releasing


Meet the requirements of USP<788> Particulate matter, ≤ 25particles/ml at 10um, ≤ 3particles/ml at 25um




TYPICAL CLEAN WATER FLOW

CARTRIDGE & CAP







ORDERING INFORMATION





www.absfil.com 57